

Project Name

Location

Prepared By



## NUVO 65-975

LED 80W UFO W/PLUG/120V

### Notes

[www] 10-11-2023 00:59:46

### General

Status	Active
Fixture Type	Shop Light
Finish	White
Wattage	80W
Lumen Output	9210L
CCT (Kelvin)	5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor; Outdoor

### Specifications

Technology	LED
Color Temperature	Natural Light
CRI	80
Voltage	120V
Beam Angle	110
Rated Hours	30000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Non-Dimmable
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	1.61
Material	Die-cast Aluminum

### Dimensions

Height (in.)	5.63
Width (in.)	8.27

### Compliance

Safety Listing	cULus
Location Rating	Wet
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

### Additional Information

Specification Note	White Powder Coating Finish
Includes	Locking Snap Hook
Warranty	3 Year Limited - Fixtures