

Project Name

Location

Prepared By



SATCO 67-102

EXIT SIGN - RED - NYC

Notes

[www] 01-15-2024 02:40:07

General

Status	Active
Fixture Type	Exit Sign
Finish	White
Wattage	2W
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Voltage	120V/277V
Operating Temperature	+10C (+50F) to +40C (+104F)
Dimmable	Non-Dimmable
Weight (lb.)	6.61
Material	Steel

Dimensions

Height (in.)	9.63
Width (in.)	14.56
Length (in.)	2.31

Compliance

Safety Listing	ULus - Certified
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	No

Additional Information

Additional Information	Input Wattage: 2.0W; Output Wattage: 0.4W; Energy Used in Maintenance Mode: 2.0W
Specification Note	20-gauge Steel, 3.6V AA300mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C; Letter Height: 8 in.; Letter Stroke: 1 in.
Includes	Mounting hardware and accessories
Warranty	2 Year Limited