

Project Name

Location

Prepared By



SATCO 67-115

REC EL EXIT SIGN - DF GR MIR

Notes

[www] 01-15-2024 02:40:07

General

Status	Active
Fixture Type	Exit Sign
Finish	Silver
Wattage	2.94W
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Voltage	120V/277V
Operating Temperature	+10C (+50F) to +40C (+104F)
Dimmable	Non-Dimmable
Lens Material	Acrylic
Weight (lb.)	5.2
Material	Aluminum

Dimensions

Height (in.)	11
Width (in.)	15.75
Length (in.)	4

Compliance

Safety Listing	ULus - Certified
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Input Wattage: 2.94W; Output Wattage: 0.4W; Energy Used in Maintenance Mode: 2.94W
Specification Note	Aluminum, Acrylic Panel, 4.8V AA300mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C; Letter Height: 6 in; Letter Stroke: 0.75 in.
Includes	Mounting hardware and accessories
Warranty	2 Year Limited