



## S11220

6W/LED/T3/78MM/830/120V/D R7S

### GENERAL SPECIFICATIONS

Shape:	T3
Wattage:	6WW
Lumen Output:	600LL
Color Temperature:	3000K
Base:	Double Contact Recessed Base



### TECHNICAL SPECIFICATIONS

Wattage:	6W	CRI:	80CRI
Volts:	120V	Lumen Output:	600L
Incandescent Equivalent:	40W	Dimmable:	Yes-Dimmable
HID Equivalent:	75W	Beam Spread:	200D
Shape:	T3	Power Factor:	0.7
Filament:	LED	Operating Temp:	-20C (-4F) to a maximum of +45C (+113F)
Base:	Double Contact Recessed Base	Enclosure Rating:	Enclosed Rated Lamp
ANSI Base:	R7S	Safety Listing:	cULus
Finish:	Clear	Technology:	LED
Housing Color:	White	Material:	Polycarbonate (PC)
Hours Rated:	15000H		
Color Temperature:	3000K		

### DIMENSIONS

MOL:	3.07"
MOD:	0.98"
Weight:	0.07

### LISTINGS

Safety Listing:	cULus
Location Rating:	Damp
Energy Star:	No
CEC Terse:	Lawful for sale in California
RoHS Compliant:	Yes
FCC Compliant:	Yes
SDS Class:	LED_Lamp

### PACKAGING

Each UPC:	045923112201	Inner UPC:	20045923112205	Case UPC:	10045923112208
Each Quantity:	1	Inner Quantity:	12	Case Quantity:	48
Each Dimensions:	3.70 x 0.20 x 5.51"	Inner Dimensions:	12.20 x 7.87 x 3.15"	Case Dimensions:	13.78 x 12.80 x 6.89"

110 Heartland Blvd.  
Brentwood, NY 11717  
PH 631-243-2022  
FX 631-243-2027

Distribution Centers  
New York, Florida,  
Texas, Washington,  
California, Puerto Rico

National Toll-Free  
800-43-SATCO  
(800-437-2826)  
www.satco.com

Copyright 2021  
Satco Products, Inc.  
All Rights Reserved  
August 6, 2021