

Project Name

Location

Prepared By



SATCO S11225

8T10/LED/HL/940/FR/DIM/CD

Notes

[www] 07-11-2022 03:01:10

General

Status	Active
Watts	8W
Incandescent Equivalent	60W
Volts	120V
Shape	T10
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90
Lumens	900L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Tubular
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---

Physical

MOL	4.02
MOD	1.26
Photocell	No
Weight (lb.)	0.28

Additional Information

Additional Info	75W Halogen replacement
Warranty	3 Year Limited - 4 hr per day

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes