

Project Name

Location

Prepared By



SATCO S11234

5W/LED/G9/830/CL/120V/DIM

Notes

[www] 11-21-2022 00:39:09

General

Status	Active
Watts	5W
Incandescent Equivalent	40W
Volts	120V
Shape	T4
Base	G9 Double Loop
ANSI Base	G9
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80
Lumens	550L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	LED
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable or Triac
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.13
MOD	0.75
Housing Color	Clear
Weight (lb.)	0.06

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp