

Project Name

Location

Prepared By



SATCO S11277

15PAR38/LED/RGB/TW/T20/SF

Notes

[www] 11-22-2021 02:57:41

General

Status	Active
Watts	15W
Incandescent Equivalent	90W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	90
Lumens	1200L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.00
MOD	4.72
Housing Color	White
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Weight (lb.)	0.33

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Pending
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

