

Project Name

Location

Prepared By



Notes

[www] 06-14-2021 17:39:07

General

Status	Active
Watts	12
Incandescent Equivalent	75
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	80
Lumens	1100
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	> 0.5

Physical

MOL	4.41
MOD	2.36
Housing Color	White
Weight (lb.)	0.12

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp