

Project Name

Location

Prepared By

SATCO S11442

16PAR38/LED/GROW/120V

Notes

[www] 08-02-2021 00:20:22

General

Status	Active
Watts	16W
Incandescent Equivalent	75W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3500
Temperature	Neutral White
CRI	80
Lumens	1100L
Beam Spread	80
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60 Hz
Candlepower	1200
Power Factor	0.5
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5
MOD	4.72
Housing Color	Green
Weight (lb.)	0.33

Additional Information

Rated For Enclosed Fixture	Yes
Specification Note	PPF is 21.8
Warranty	3 Year Limited - 4 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp