



S11451

5A19/LED/830/120V/D/4PK

GENERAL SPECIFICATIONS

Shape:	A19
Wattage:	5W
Lumen Output:	450LL
Color Temperature:	3000K
Base:	Medium



TECHNICAL SPECIFICATIONS

Wattage:	5W	CRI:	80CRI
Volts:	120V	Lumen Output:	450L
Incandescent Equivalent:	40W	Dimmable:	Yes-Dimmable
Shape:	A19	Dimming Function:	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Filament:	LED	Beam Spread:	230D
Base:	Medium	Operating Temp:	-20C (-4F) to a maximum of +45C (+113F)
ANSI Base:	E26	Enclosure Rating:	Enclosed Rated Lamp
Finish:	Frost	Safety Listing:	cULus - Listed
Housing Color:	White	Technology:	LED
Hours Rated:	15000H	Material:	Polycarbonate (PC) / High Heat Conductive Plastic Housing
Color Temperature:	3000K		

DIMENSIONS

MOL:	4.17"
MOD:	2.38"
Weight:	0.31

LISTINGS

Safety Listing:	cULus - Listed
Location Rating:	Damp
Energy Star:	Pending
UL File Listing:	US&CN E335148
FCC Compliant:	Yes
RoHS Compliant:	Yes
SDS Class:	LED_Lamp

PACKAGING

Each UPC:	045923101519
Each Quantity:	1
Each Dimensions:	7.24 x 2.44 x 4.69"

Case UPC:	10045923101516
Case Quantity:	12
Case Dimensions:	15.16 x 7.48 x 9.84"

110 Heartland Blvd.
Brentwood, NY 11717
PH 631-243-2022
FX 631-243-2027

Distribution Centers
New York, Florida,
Texas, Washington,
California, Puerto Rico

National Toll-Free
800-43-SATCO
(800-437-2826)
www.satco.com

Copyright 2022
Satco Products, Inc.
All Rights Reserved
March 30, 2022