

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S11477

5B11/DUSK/DAWN/927

Notes

[www] 06-07-2023 00:27:23

General

Status	Active
Watts	5W
Incandescent Equivalent	60W
Volts	120V
Shape	B11
Base	Candelabra
ANSI Base	E12
Finish	White
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	500L
Beam Spread	280
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Candle
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Position	Universal
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	4.02
MOD	1.38
Photocell or Sensor	Has Photocell
Weight (lb.)	0.08

Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes

