

Project Name

Location

Prepared By



SATCO S11485

36PS30/LED/850/120V/DIM/E39

Notes

[www] 04-07-2023 14:29:37

General

Status	Active
Watts	36W
Incandescent Equivalent	300W
Volts	120V
Shape	PS30
Base	Mogul
ANSI Base	E39
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	4500L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Note	120V only
Power Factor	0.98
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	7.91
MOD	3.74
Housing Color	White
Weight (lb.)	0.71

Additional Information

Additional Info	For use in: Houses of Worship, Hospitality, Warehouses, Barns, Garages, Workshops, etc
Rated For Enclosed Fixture	No
Installation Notes	Not approved for totally enclosed fixtures
Specification Note	Smooth dimming below 10%
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
NSF Approved	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes

