

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S11490

10/22/34PS25/3WAY/LED/827/E39D

Notes

[www] 01-15-2024 02:40:09

General

Status	Active
Watts	10W/22W/34W
Incandescent Equivalent	100W/200W/300W
Volts	120V
Shape	PS25
Base	Mogul DC
ANSI Base	E39d
Finish	White
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	80
Lumens	1300L/2900L/4100L
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.92
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	7.09
MOD	3.11
Housing Color	White
Weight (lb.)	0.57

Additional Information

Additional Info	Three way lamp
Rated For Enclosed Fixture	Yes
Three Way	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - 3-Way Lamp
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp