SATCO NUVO

Project Name

ocation Prepared By



HAAGE NOT AVAILABLE

SATCO S11493

10/22/34PS25/3WAY/LED/850/E39D

Notes

| Status | Active |
|-------------------------|-------------------|
| Watts | 10W/22W/34W |
| Incandescent Equivalent | 100W/200W/300W |
| Volts | 120V |
| Shape | PS25 |
| Base | Mogul DC |
| ANSI Base | E39d |
| Finish | White |
| CCT (Kelvin) | 5000K |
| Temperature | Natural Light |
| CRI | 80 |
| Lumens | 1300L/2900L/4100L |
| Beam Spread | 220 |
| Dimmable | Non-Dimmable |
| Hours Rated | 25000 |
| Lamp Type | Type A |
| Technology | LED |

| Electrical | |
|-----------------------|-----------------------------|
| Operating Frequency | 60Hz |
| Power Factor | 0.92 |
| Operating Temperature | -25C (-13F) to +45C (+113F) |
| Physical | |

| Physical | |
|---------------|-------|
| MOL | 7.09 |
| MOD | 3.11 |
| Housing Color | White |
| Weight (lb.) | 0.57 |

| Additional Information | |
|----------------------------|--------------------------------|
| Additional Info | Three way lamp |
| Rated For Enclosed Fixture | Yes |
| Three Way | Yes |
| Warranty | 5 Year Limited - 10 hr per day |

| Compliance | |
|------------------------|-------------------------------|
| Safety Listing | cULus - Listed |
| Location Rating | Damp |
| Energy Star | No |
| CA T20 / T24 Rationale | Exempt - 3-Way Lamp |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |
| | |

