

Project Name

Location

Prepared By



**Notes**

[www] 11-01-2023 00:12:53

**General**

Status	Active
Finish	White
Wattage	9W
Style	Utility
CCT (Kelvin)	2000K-5000K
Color Temperature	Warm to Cool White/Color Changeable
Width (in.)	5
Height (in.)	1
Indoor or Outdoor Fixture	Indoor

**Smart Product Info**

IOT Enabled	Yes
Voice Assistants Supported	Google Home;Alexa;Siri;SmartThings

**Specifications**

Technology	LED
CRI	90
Lumen Output	540L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	110
Operating Temperature	-20C (-4F) to +40C (+104F)
IC Rated	Yes
Weight (lb.)	0.88
Fixture Shape	Round
Fixture Material	Aluminum
Fixture Type	Remote Driver LED Downlight

**Compliance**

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2494955
Air Tight Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

**Additional Information**

Installation Notes	Driver Dimensions: 3.46 Inches Long x 3.46 Inches Wide x 1.44 Inches High
Warranty	5 Year Limited - Fixtures

