

Project Name

Location

Prepared By



**Notes**

[www] 11-01-2023 00:12:53

**General**

|                           |                                     |
|---------------------------|-------------------------------------|
| Status                    | Active                              |
| Finish                    | White                               |
| Wattage                   | 12W                                 |
| Style                     | Utility                             |
| CCT (Kelvin)              | 2000K-5000K                         |
| Color Temperature         | Warm to Cool White/Color Changeable |
| Width (in.)               | 7.17                                |
| Height (in.)              | 1.25                                |
| Indoor or Outdoor Fixture | Indoor                              |

**Smart Product Info**

|                            |                                    |
|----------------------------|------------------------------------|
| IOT Enabled                | Yes                                |
| Voice Assistants Supported | Google Home;Alexa;Siri;SmartThings |

**Specifications**

|                       |                             |
|-----------------------|-----------------------------|
| Technology            | LED                         |
| CRI                   | 90                          |
| Lumen Output          | 750L                        |
| Rated Hours           | 50000                       |
| Voltage               | 120V                        |
| Dimmable              | Yes-Dimmable                |
| Dimming Note          | Only with Starfish App      |
| Beam Angle            | 110                         |
| Operating Temperature | -20C (-4F) to +40C (+104F)  |
| IC Rated              | Yes                         |
| Weight (lb.)          | 1.19                        |
| Fixture Shape         | Round                       |
| Fixture Material      | Aluminum                    |
| Fixture Type          | Remote Driver LED Downlight |

**Compliance**

|                        |                                       |
|------------------------|---------------------------------------|
| Safety Listing         | cETLus                                |
| Location Rating        | Wet                                   |
| Energy Star            | Yes                                   |
| ES Unique ID           | ESID-2495000                          |
| Air Tight Rated        | Yes                                   |
| CA T20 / T24 Rationale | California T24 2016 - 2022 JA8 Listed |
| California Status      | Lawful for sale in California         |
| Title 20 / 24 Status   | California T24 Listed                 |
| California Prop 65     | Lead                                  |
| RoHS Compliant         | Yes                                   |
| FCC Compliant          | Yes                                   |
| SDS Sheet              | LED_Fixture                           |

**Additional Information**

|                    |   |
|--------------------|---|
| Installation Notes | Driver Dimensions: 3.46 Inches Long x 3.46 Inches Wide x 1.44 Inches High |
| Warranty           | 5 Year Limited - Fixtures   |

