

Project Name

Location

Prepared By



# SATCO S11743

9.5/T8/LED/48-850/DR

## Notes

[www] 01-17-2022 02:16:05

### General

Status	Active
Watts	9.5W
Fluorescent Equivalent	32W/30W/28W/25W
Volts	120V-277V
Ballast Type	Type A
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48.00
Finish	Gloss
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	82
Lumens	1740L
Beam Spread	210
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

### Electrical

Ballasting Requirements	Ballast required. Direct Replacement-for use on Instant Start and Rapid Start ballasts with no rewiring required. May not be compatible with every ballast. Refer to the ballast compatibility chart
Operating Frequency	50/60 Hz
Dimming Note	Check Ballast MFG for Dimmer Compatibility; Only in Type A mode; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	48.00
MOD	1.00
Material	Glass
Housing Color	White
Weight (lb.)	0.42

### Additional Information

Specification Note	Surge Protection
Warranty	5 Year Limited - T8 LED Bulbs

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes

DLC ID	PL2JWH754LKM
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

