

Project Name

Location

Prepared By



SATCO S11747

17T8/LED/48-850/BP/DE/347V

Notes

[www] 07-11-2022 03:01:10

General

Status	Active
Watts	17W
Volts	347V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48.00
Finish	Gloss White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	82
Lumens	2200L
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	T8
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	47.78
MOD	1.00
Material	Plastic
Lens Finish	Frost
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.44

Additional Information

Additional Info	CANADA ONLY
Tube Guard Use	Yes
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cUL - Classified; cUL - Certified; cRU - Recognized Component
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-WQJYVL
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
Flicker Free	Yes

