

SATCO S11760

10T8/LED/24-CCT/DM/BP-DR

Notes

California Status

General	
Status	Active
Watts	10W
Incandescent Equivalent	125W
Fluorescent Equivalent	32W/30W/28W/25W
Volts	120V-277V
Ballast Type	Type A/B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	24
Finish	White
CCT (Kelvin)	3500K/4000K/5000K
Temperature	Neutral White to Natural Light
CRI	83
Lumens	1425L/1450L/1450L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED
Electrical	
Ballasting Requirements	Ballast required (Type A) or Ballast Bypass (Type B)
Operating Frequency	50/60Hz
Dimming Note	Only in Type A mode; Check Ballast MFG for Dimmer Compatibility
Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)
Physical	
MOL	23.78
MOD	1
Material	Glass / Plastic
Lens Finish	Frost
Lens Material	Glass
Housing Color	White
Additional Information	
Shatter-Proof Type	PET Coated
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs
Compliance	
Safety Listing	cULus - Listed; cULus - Classified; cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-I8R2WN
CA T20 / T24 Rationale	Exempt - Base Not Regulated

Lawful for sale in California

Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

Copyright 2023 Satco Products, Inc. All Rights Reserved

For More Information Visit: https://www.satco.com/



