

Project Name

Location

Prepared By



SATCO S11764

9T8/LED/24-5CCT/BP/SE-DE

Notes

[www] 05-06-2023 01:09:33

General

Status	Active
Watts	9W
Fluorescent Equivalent	17W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	24.00
Finish	White
CCT (Kelvin)	3000K/3500K/4000K/5000K/6500K
Temperature	Warm White to Daylight
CRI	80
Lumens	1150L/1150L/1250L/1250L/1250L
Beam Spread	210
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Operating Frequency	50/60Hz
Power Factor	0.9
THD	<25%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	23.17
MOD	1.00
Material	Glass / Plastic
Lens Finish	Frosted
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.25

Additional Information

Additional Info	Non CCT Selectable options are S39900-S39903
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus - Classified; cULus - Certified; cRUus - Recognized Component
Location Rating	Damp
DLC Approved	Yes
DLC ID	S-N3X0KC
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes



