

Project Name

Location

Prepared By



# SATCO S11766

14T8/LED/48-5CCT/BP/SE-DE

## Notes

[www] 05-06-2023 01:09:33

### General

Status	Active
Watts	14W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48.00
Finish	White
CCT (Kelvin)	3000K/3500K/4000K/5000K/6500K
Temperature	Warm White to Daylight
CRI	80
Lumens	1700L/1700L/1800L/1800L/1800L
Beam Spread	210
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

### Electrical

Operating Frequency	50/60Hz
Power Factor	0.9
THD	<25%
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	47.17
MOD	1.00
Material	Glass / Plastic
Lens Finish	Frosted
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.45

### Additional Information

Additional Info	Non CCT Selectable options are S39913-S39916
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

### Compliance

Safety Listing	cULus - Classified; cRUus - Recognized Component
Location Rating	Damp
DLC Approved	Yes
DLC ID	S-9MV7GT
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

