

Project Name

Location

Prepared By



## SATCO S11770

6A19/LED/3CCT/E26/120V

### Notes

[www] 06-17-2020 22:42:05

### General

Status	Active
Watts	6W
Incandescent Equivalent	40W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	470L
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	4.41
MOD	2.36
Housing Color	White
Weight (lb.)	0.08

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp