

Project Name

Location

Prepared By



## SATCO S11795

12A19/LED/5CCT/GU24/120V

### Notes

[www] 06-17-2020 22:42:05

### General

Status	Active
Watts	12W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Bi Pin GU24
ANSI Base	GU24
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	1100L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Temperature	-20C (-4F) to +40C (+104F)

### Physical

MOL	4.29
MOD	2.36
Housing Color	White
Weight (lb.)	0.11

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp