

Project Name

Location

Prepared By



SATCO S11870

12WLED/DW/4/CCT-SEL/RND/RD/WH

Notes

[www] 05-24-2023 02:30:00

General

Status	Active
Wattage	12W
Voltage	120V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Lumen Output	850L

Specifications

Technology	LED
CRI	90
Beam Angle	112
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable

Dimensions

Width (in.)	5.06
Height (in.)	1.25
Weight (lb.)	0.92

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2408267
IC Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Installation Notes	Driver Dimensions: 4.27 x 3.62 x 1.44
Warranty	5 Year Limited - Fixtures