



**S11957**

24T8/LED/96-835/BP/FA8

**GENERAL SPECIFICATIONS**

Shape:	T8
Wattage:	24WW
Color Temperature:	3500K
Length:	94.00"
Base:	Single Pin



**TECHNICAL SPECIFICATIONS**

Wattage:	24W	Dimmable:	Non-Dimmable
Volts:	120V-277V	Beam Spread:	210D
Shape:	T8	Ballasting Requirements:	Ballast Bypass
Filament:	LED	Ballast Type:	Type B
Base:	Single Pin	Single / Dual End:	Double Ended
ANSI Base:	FA8	Shatter Proof Type:	PET Coated
Finish:	White	Safety Listing:	cULus
Hours Rated:	50000H	Technology:	LED
Color Temperature:	3500K		
CRI:	82CRI		
Lumen Output:	3200L		

**DIMENSIONS**

MOL:	94.00"
MOD:	1.00"
Weight:	0.88

**LISTINGS**

Safety Listing:	cULus
Location Rating:	Damp
Energy Star:	No
CEC Terse:	Lawful for sale in California
FCC Compliant:	Yes
NSF Approved:	Yes

**PACKAGING**

Each UPC:	045923119576
Each Quantity:	1
Each Dimensions:	94.00 x 1.00 x 1.00"

Case UPC:	10045923119573
Case Quantity:	10
Case Dimensions:	95.87 x 7.56 x 3.86"

110 Heartland Blvd.  
Brentwood, NY 11717  
PH 631-243-2022  
FX 631-243-2027

Distribution Centers  
New York, Florida,  
Texas, Washington,  
California, Puerto Rico

National Toll-Free  
800-43-SATCO  
(800-437-2826)  
www.satco.com

Copyright 2021  
Satco Products, Inc.  
All Rights Reserved  
August 4, 2021