

Project Name

Location

Prepared By



SATCO S12437

10.5A19/CL/LED/930/120V/4PK

Notes

[www] 10-25-2021 04:00:40

General

| | |
|-------------------------|--------------|
| Status | Active |
| Watts | 10.5W |
| Incandescent Equivalent | 75W |
| Volts | 120V |
| Shape | A19 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 3000 |
| Temperature | Soft White |
| CRI | 90 |
| Lumens | 1100L |
| Beam Spread | 320 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Lamp Type | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|---|
| Operating Frequency | 60 Hz |
| Dimming Type | Forward Phase |
| Power Factor | 0.7 |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |

Physical

| | |
|--------------|------|
| MOL | 4.02 |
| MOD | 2.36 |
| Weight (lb.) | 0.08 |

Additional Information

| | |
|----------------------------|-------------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited - 4 hr per day |

Compliance

| | |
|-------------------|-----------------|
| Safety Listing | cULus Listed |
| Location Rating | Wet |
| Energy Star | Pending |
| California Status | Lawful for sale |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |