

Project Name

Location

Prepared By



SATCO S12439

11A19/SW/LED/930/120V/4PK

Notes

[www] 10-25-2021 04:00:40

General

Status	Active
Watts	11W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Soft White
CCT (Kelvin)	3000
Temperature	Soft White
CRI	90
Lumens	1100L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.02
MOD	2.36
Weight (lb.)	0.08

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 4 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	Pending
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp