

Project Name

Location

Prepared By



SATCO S12443

12.5A19/CL/LED/930/120V/4PK

Notes

[www] 10-25-2021 04:00:40

General

Status	Active
Watts	12.5W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000
Temperature	Soft White
CRI	90
Lumens	1500L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Physical

MOL	4.41
MOD	2.36
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited - 4 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp