

Project Name

Location

Prepared By



SATCO S12464

8A19/CL/LED/E26/940/4PK/120V

Notes

[www] 05-15-2020 01:50:09

General

Status	Active
Watts	8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90
Lumens	800L
Beam Spread	280
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.33
MOD	2.36
Housing Color	Clear
Weight (lb.)	0.07

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2405826
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes