

Project Name

Location

Prepared By



SATCO S13153

100W/LED/HID-HB/850/120-277V/D

Notes

[www] 11-14-2021 22:13:46

General

Status	Active
Watts	100W
Volts	120V-277V
Shape	N/A
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	82
Lumens	15500L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	HID
Technology	LED
Min Compartment Size	Diameter: 11.81 in. Height: 13.78 in.
Ballasting Requirements	Ballast Bypass

Electrical

Operating Frequency	50/60 Hz
Burning Position	Vertical with Base Up
Surge Protection	Built-in surge protection - 6KV
Operating Temperature	-40C (-40F) to a maximum of +60C (+140F)

Physical

MOL	8.15
MOD	6.34
Lens Finish	Clear
Lens Material	Glass
Housing Color	White
Weight (lb.)	2.09

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified; cULus Listed
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp