

Project Name

Location

Prepared By



**Notes**

[www] 11-30-2023 01:02:46

**General**

|                         |                                |
|-------------------------|--------------------------------|
| Status                  | Active                         |
| Watts                   | 30W                            |
| Incandescent Equivalent | 125W                           |
| Fluorescent Equivalent  | 85W                            |
| Volts                   | 120V-277V                      |
| Ballast Type            | Type B                         |
| Shape                   | T8                             |
| Base                    | Recessed Double Contact HO/VHO |
| ANSI Base               | R17d                           |
| Nominal Length          | 72                             |
| Finish                  | White                          |
| CCT (Kelvin)            | 4000K/5000K/6500K              |
| Temperature             | Cool White to Daylight         |
| CRI                     | 83                             |
| Lumens                  | 4200L/4350L/4150L              |
| Beam Spread             | 360                            |
| Dimmable                | Non-Dimmable                   |
| Hours Rated             | 50000                          |
| Lamp Type               | Linear                         |
| Technology              | LED                            |

**Electrical**

|                         |                            |
|-------------------------|----------------------------|
| Ballasting Requirements | Ballast Bypass             |
| Operating Frequency     | 50/60Hz                    |
| Power Factor            | 0.9                        |
| THD                     | 25%                        |
| Operating Temperature   | -20C (-4F) to +45C (+113F) |

**Physical**

|               |                    |
|---------------|--------------------|
| MOL           | 69.81              |
| MOD           | 1.13               |
| Material      | Polycarbonate (PC) |
| Lens Finish   | Frost              |
| Lens Material | Plastic            |
| Weight (lb.)  | 1.15               |

**Additional Information**

|                            |                               |
|----------------------------|-------------------------------|
| Tube Guard Use             | No                            |
| Rated For Enclosed Fixture | Yes                           |
| Warranty                   | 5 Year Limited - T8 LED Bulbs |

**Compliance**

|                        |   |
|------------------------|---|
| Safety Listing         | cULus - Classified; cRUus - Recognized Component; ETLus - SANITATION RECOGNIZED COMPONENT |
| Location Rating        | Damp  |
| Energy Star            | No  |
| DLC Approved           | No  |
| CA T20 / T24 Rationale | Exempt - Base Not Regulated   |
| California Status      | Lawful for sale in California   |
| Title 20 / 24 Status   | Lawful for sale   |

|                |   |
|----------------|---|
| RoHS Compliant | Yes                                     |
| FCC Compliant  | Yes                                     |
| NSF Approved   | ETL Sanitation listed (conforms to NSF) |
| SDS Sheet      | LED_Lamp                                |

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

