

Project Name

Location

Prepared By



SATCO S18400

4.5W/LED/CFL/827/G23/BP

Notes

[www] 08-10-2020 02:07:43

General

Status	Active
Watts	4.5
Fluorescent Equivalent	5W/7W/9W
Volts	120V-277V
Ballast Type	Type B
Shape	PL
Base	G23
ANSI Base	G23
Finish	Frosted
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	450
Beam Spread	360
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	PL
Burning Position	Universal
Technology	LED

Electrical

Operating Frequency	50/60Hz
Power Factor	0.9
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	6.54
MOD	1.28
Housing Color	White
Weight (lb.)	0.55

Additional Information

Enclosure Rating	Enclosed Rated Lamp
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp