

Project Name

Location

Prepared By



Notes

[www] 11-20-2023 01:02:46

General

Status	Active
Watts	13W
Incandescent Equivalent	50W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type A/B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	22.5
Finish	White
CCT (Kelvin)	3500K/4000K/5000K
Temperature	Neutral White to Natural Light
CRI	80
Lumens	1900L/1975L/1950L
Beam Spread	160
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	U-Bend
Technology	LED

Electrical

Ballasting Requirements	Ballast required (Type A) or Ballast Bypass (Type B)
Operating Frequency	50/60Hz
Dimming Note	Only in Type A mode; Check Ballast MFG for Dimmer Compatibility
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	22.6
MOD	1
Leg Spacing	6
Material	Plastic
Lens Finish	Frost
Lens Material	Plastic
Housing Color	White

Additional Information

Additional Info	Replaces FB32T8/U6
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs

Compliance

Safety Listing	cULus - Listed; cULus - Classified; cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-R4NQ0V

CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

