

Project Name

Location

Prepared By



## SATCO S21245

6G25/LED/CL/927/120V/2PK

### Notes

[www] 07-11-2022 03:01:10

### General

|              |              |
|--------------|--------------|
| Status       | Active       |
| Watts        | 6W           |
| Volts        | 120V         |
| Shape        | G25          |
| Base         | Medium       |
| ANSI Base    | E26          |
| Finish       | Clear        |
| CCT (Kelvin) | 2700K        |
| Temperature  | Warm White   |
| CRI          | 90           |
| Lumens       | 500L         |
| Beam Spread  | 300          |
| Dimmable     | Yes-Dimmable |
| Hours Rated  | 15000        |
| Technology   | LED          |

### Electrical

|                       |   |
|-----------------------|---|
| Operating Frequency   | 60 Hz                                   |
| Power Factor          | >0.7                                    |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |

### Physical

|              |       |
|--------------|-------|
| MOL          | 4.45  |
| MOD          | 3.15  |
| Weight (lb.) | 0.176 |

### Additional Information

|                            |                |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes            |
| Warranty                   | 3 Year Limited |

### Compliance

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cETLus                        |
| Location Rating        | Wet                           |
| Energy Star            | Pending                       |
| CA T20 / T24 Rationale | T20 Listed                    |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |