

Project Name

Location

Prepared By



SATCO S21250

4.5G40/WH/LED/E26/927/120V

Notes

[www] 07-11-2022 03:01:10

General

Status	Active
Watts	4.5W
Incandescent Equivalent	40W
Volts	120V
Shape	G40
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	350L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	>0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	6.54
MOD	4.88
Weight (lb.)	0.209

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes