

Project Name

Location

Prepared By



SATCO S21319

5.5CA10/LED/940/CL/120V/E26

Notes

[www] 07-11-2022 03:01:11

General

| | |
|-------------------------|--------------|
| Status | Active |
| Watts | 5.5W |
| Incandescent Equivalent | 60W |
| Volts | 120V |
| Shape | CA10 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 4000K |
| Temperature | Cool White |
| CRI | 90 |
| Lumens | 500L |
| Beam Spread | 300 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Technology | LED |

Electrical

| | |
|-----------------------|---|
| Operating Frequency | 60 Hz |
| Power Factor | >0.7 |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |

Physical

| | |
|--------------|-------|
| MOL | 4.33 |
| MOD | 1.38 |
| Weight (lb.) | 0.044 |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|------------------------|-------------------------------|
| Safety Listing | cETLus |
| Location Rating | Wet |
| Energy Star | Pending |
| CA T20 / T24 Rationale | T20 Listed |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| RoHS Compliant | Yes |