

Project Name

Location

Prepared By



SATCO S21366

4B11/LED/927/CL/120V/E12/3PK

Notes

[www] 07-11-2022 03:01:11

General

Status	Active
Watts	4W
Volts	120V
Shape	B11
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	350L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	>0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	3.97
MOD	1.38
Weight (lb.)	0.106

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes