

Project Name

Location

Prepared By



SATCO S21371

4T6.5/LED/CL/940/120V/E17

Notes

[www] 02-24-2023 02:01:50

General

Status	Active
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	T6.5
Base	Intermediate
ANSI Base	E17
Finish	Clear
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90
Lumens	400L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	>0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5.12
MOD	0.79
Housing Color	Clear
Weight (lb.)	0.71

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Wet
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes