

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S21818

3B11/LED/927/FR/120V/E12/2CD

Notes

[www] 05-15-2023 01:50:10

General

Status	Active
Watts	3W
Incandescent Equivalent	25W
Volts	120V
Shape	B11
Base	Candelabra
ANSI Base	E12
Finish	Frost
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	200L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to +45C (+113F)
-----------------------	----------------------------

Physical

MOL	3.97
MOD	1.38
Weight (lb.)	0.071

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2407347
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes

