

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

## SATCO S21838

5.5B11/LED/927/FR/120V/E26/2CD

### Notes

[www] 05-15-2023 01:50:10

### General

Status	Active
Watts	5.5W
Incandescent Equivalent	60W
Volts	120V
Shape	B11
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	500L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

### Electrical

Operating Temperature	-20C (-4F) to +45C (+113F)
-----------------------	----------------------------

### Physical

MOL	3.58
MOD	1.38
Weight (lb.)	0.071

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2407745
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes