

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

# SATCO S21840

4CA10/LED/927/CL/120V/E12/2CD

**Notes**

[www] 05-15-2023 01:50:10

**General**

Status	Active
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	CA10
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	350L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

**Electrical**

Operating Temperature	-20C (-4F) to +45C (+113F)
-----------------------	----------------------------

**Physical**

MOL	4.72
MOD	1.38
Weight (lb.)	0.071

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

**Compliance**

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2408090
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes