

Project Name

Location

Prepared By



Notes

[www] 04-18-2022 00:26:33

General

Status	Active
Watts	80W
HID Equivalent	250W
Volts	120V-277V
Base	Mogul Extended
ANSI Base	EX39
Finish	Translucent White
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	80
Lumens	10000L
Beam Spread	115
Dimmable	Yes-Dimmable
Hours Rated	35000
Lamp Type	Hi-Bay
Technology	LED
Min Compartment Size	Length: 13.5 in. Width: 13.5 in. Height: 12 in.

Electrical

Operating Frequency	50-60 Hz
Candlepower	3000
Dimming Note	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Power Factor	0.98/0.92
Surge Protection	Built-in surge protection - 6KV
Operating Temperature	-40C (-40F) to a maximum of +60C (+140F)

Physical

MOL	10.12
MOD	7.48
Housing Color	White
Weight (lb.)	1.76

Additional Information

Rated For Enclosed Fixture	Yes
Specification Note	Fixture has a built-in dimming control feature
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Classified; cULus - Certified
Location Rating	Damp
Energy Star	No
FCC Compliant	Yes
SDS Sheet	LED_Lamp