

Project Name

Location

Prepared By



SATCO S23145

120W/LED/CCT/100-277V/EX39

Notes

[www] 05-07-2022 02:41:07

General

Status	Active
Watts	120W
HID Equivalent	600W
Volts	100V-277V
Base	Extended Mogul
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
CRI	80
Lumens	11200L/14000L/16800L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corn-cob
Technology	LED
Min Compartment Size	Length: 9.85 in. Width: 9.85 in. Height: 12.60 in.
Ballasting Requirements	Ballast Bypass

Electrical

Operating Frequency	50-60 Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Power Factor	>0.9
Burning Position	Base Up or Base Down Only
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	11.33
MOD	5.11
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	3.48

Additional Information

Additional Info	Power selectable
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Warranty	5 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus listed; cULus classified
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

