

Project Name

Location

Prepared By



# SATCO S23147

22W/LED/CCT/100-277V/E26

## Notes

[www] 05-07-2020 02:41:07

### General

Status	Active
Watts	22W
HID Equivalent	100W
Volts	100V-277V
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
CRI	80
Lumens	2240L/2520L/3080L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Ballasting Requirements	Ballast Bypass

### Electrical

Operating Frequency	50-60 Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Power Factor	>0.9
Burning Position	Base Up, Base Down, or Horizontal
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

### Physical

MOL	6.89
MOD	2.32
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	0.66

### Additional Information

Additional Info	Power selectable
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Warranty	5 Year Limited - 12 hr per day

### Compliance

Safety Listing	cULus listed; cULus classified
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - >2600 Lumens
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

