

Project Name

Location

Prepared By



General

Status	Active
Watts	18
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	4100
Temperature	Cool White
CRI	62
Lumens	1320
Beam Spread	360
Hours Rated	7500
Lamp Type	Linear
Technology	Fluorescent

Physical

MOL	29.22
MOD	1.04
Weight (lb.)	0.0032

Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp

Notes

[www] 03-09-2021 01:43:25