

Project Name

Location

Prepared By



# SATCO S26517

F30T8/CW

## Notes

[www] 01-29-2021 11:42:02

### General

Status	Active
Watts	30
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	4100
CRI	62
Lumens	2100
Beam Spread	360
Hours Rated	20000
Lamp Type	Linear
Technology	Fluorescent

### Physical

MOL	35.22
MOD	1.04

### Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp