

Project Name

Location

Prepared By



General

Status	Active
Watts	30
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	6500
Temperature	Daylight
CRI	74
Lumens	1850
Beam Spread	360
Hours Rated	20000
Technology	Fluorescent

Physical

MOL	35.22
MOD	1.04

Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp

Notes

[www] 01-29-2021 11:42:02