

Project Name

Location

Prepared By



SATCO S26562

F15T12/CW

Notes

[www] 03-09-2021 01:43:25

General

Status	Active
Watts	15
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	4100
Temperature	Cool White
CRI	62
Lumens	650
Beam Spread	360
Hours Rated	8000
Lamp Type	Linear
Technology	Fluorescent

Physical

MOL	17.22
MOD	1.50
Weight (lb.)	0.0049

Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp