

Project Name

Location

Prepared By



# SATCO S26565

F20T12/CW

**Notes**

[www] 01-29-2021 11:42:02

**General**

Status	Active
Watts	20
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	4100
CRI	62
Lumens	1200
Beam Spread	360
Hours Rated	10000
Lamp Type	Linear
Technology	Fluorescent

**Physical**

MOL	23.22
MOD	1.50

**Compliance**

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp