

Project Name

Location

Prepared By

**SATCO S26567**

F20T12/WW

General

Status	Active
Watts	20
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	3000
Temperature	Warm White
CRI	52
Lumens	1300
Beam Spread	360
Hours Rated	10000
Lamp Type	Linear
Technology	Fluorescent

Physical

MOL	23.22
MOD	1.50

Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp

Notes

[www] 01-29-2021 11:42:02